

SPECIFICATIONS

Internal Finish: Type 304 stainless steel, #4

External surfaces: RAL 7035

Wall thickness: 0.105" (2.6 mm)

Feedthrough: DN 40 ISO-KF blank and 3/8" compression bulkhead

Internal Power: Electrical feedthrough

Internal Power: Fuse protected 6 outlet power strip

Shelving: 3 x Height adjustable 304 stainless steel #4 finish

Plumbing: 304 stainless steel tubing

Filters: 1 x Inlet/ 1 x Outlet HEPA (99.99% vs 0.3 micron MPPS)

Lighting: External Fluorescent light

Power: 100-120 or 200-240 VAC 50/60 Hz 20 Amp

Overall System Leak Rate: <0.05vol%/h (ISO 10648-2)

Modular box design

Large Antechamber, 15" (381 mm) internal diameter x 24" (609 mm) internal length

Bolt on left or right side

Internal tray: 304 stainless steel #4 surface finish

Automatic control: Evacuate/refill 1-9 Cycles

Leak rate: < 10⁻⁵ mbar l/s

Small Antechamber, 6" (152 mm) internal diameter x 17.3" (441 mm) internal length

Internal tray: 304 stainless steel #4 surface finish

Manual evacuate/refill valve

Leak rate: < 10⁻⁵ mbar l/s

Tempered safety glass window 3/8" (9.5 mm) thick.

Oval glove ports: Black Delrin, 8" glove port
Internal glove port cover
0.015" (0.4mm) thick butyl rubber gloves, hand size 9.75

PureLab HE Gas Management System

Purifies, recirculates, and analyzes inert atmosphere, available as single and dual column system, with and without external solvent removal

<1ppm O₂ and <1ppm H₂O purity level

O₂ capacity = 43 L per purifier column

H₂O capacity = 1800 g per purifier column

Variable speed circulation blower: 120 cfm max flow rate blower

Siemens SIMATIC S7-1200 PLC control system

Siemens KTP700 7" (177.8 mm) color touch screen HMI

Automatic pressure control: (+/- 15 mbar)

Manual pressure control: Footswitch

Fully automatic regeneration sequence.

Auto Purge valve: O₂ Level, Timer or manually controlled

Vacuum pump: 10 cfm (17 m³/h) rotary vane pump with oil mist eliminator & oil return kit

Integrated oxygen analyzer: Range 0-1000 ppm
EOS-2 analyzer

Integrated moisture analyzer: Range 0-1000 ppm

Eco Mode Features

Vacuum pump timer: Shuts pump off for energy reduction

Automated Blower speed control: O₂ level adjusts blower speed

Approvals:



OPTIONS

- 0-1000 ppm EOS-1 Analyzer
- 0-25% Zirconia Oxygen Analyzer
- 0-1000ppm Moisture Analyzer
- 0-25% Helium in Argon Analyzer
- 0-25% Helium in Nitrogen Analyzer
- Vacuum Pumps
- Solvent Removal
- Rectangular Freezer: -35°C
Internal Volume = 20L (40L available)
- Custom Coldwell
- Numerous Antechamber Options
- Thermoelectric Box Cooling System
- Heat Exchanger
- Dry Scroll Pump
- Vacuum Ovens
- Solvent Purification Systems
- Microscope Systems
- Custom Shelving
- Electrical Feedthroughs
- Fiberoptic Feedthroughs
- RS-32/USB/Ethernet Feedthroughs
- Quartz Window for Solar Simulator Testing
- Optical View Ports for Laser Spectroscopy
- Vacuum/Gas Feedthroughs
- Custom Feedthroughs
- Door Interlocks
- Automated Doors
- Vacuum Cleaner
- Polycarbonate Window
- Evaporation System Integration
- Quick Release Window System
- Gloveport Covers
- 250°C Hot Plates
- Static Eliminator - Benchtop Style
- Inkjet Printers
- Probe Stations
- UV Ozone Cleaners
- Static Eliminator - Ceiling Mounted
- Optical View Ports for Laser Spectroscopy
- Binding Posts

SYSTEM APPLICATIONS

- Additive (3D) Manufacturing
- Aerospace
- Automotive
- Chemistry
- Lamp Manufacturing
- Lithium Ion Battery
- Medical Device
- Nuclear
- OLED
- Pharmaceutical
- Semiconductor
- Solar
- Specialty Chemical
- Thin Film
- Many other applications